INDIRECT/DIRECT BED WALL LIGHTING FOR HOSPITALS





The Amadea complements the "Silhouette Headwall System" from Modular Services.

Introducing the "Amadea[®]", our latest modular bed wall lighting system from Derungs[®] Medical Lighting. The Amadea features flexible and energy efficient four-way light distribution for meeting virtually all patient and staff requirements including indirect/direct lighting for examinations, direct lighting for reading, and a convenient night light – all in one luminaire! The Amadea is available in two lengths, 36 and 48 inches, and is easily mounted to virtually any bed wall area. A remote control and control pad is also offered with the Amadea. For hospital staff, use the convenient remote control to adjust the light levels, for connection to nursing staff call systems, and for telephone/ network access. The pad, which is controlled by the patient at bedside, quickly calls the nurse and provides simple control of the light functions. Specify a brighter choice today with Derungs Medical Lighting.

Amadea Features:

- Models are available with two energy efficient 39W or 54W T5HO fluorescent lamps for indirect/direct illumination, one 24W T5HO fluorescent lamp for direct illumination, and a 7W incandescent lamp for night lighting. The fluorescent lamps have a rated life of 20,000 hours and are supplied in 4100K.
- Choose either the "WSS model" offering a shorter 36-inch length and a light opening of 34 inches, or the longer "WLS model" providing a 48-inch length with a light opening of 46 inches for illuminating larger hospital room areas.
- Electronic ballasts increase energy efficiency, provide flicker-free illumination and are pre-wired for quick and convenient installation.
- Four-way light distribution includes indirect/direct lighting for examinations, direct lighting for reading, and a convenient night light.
- A remote control is offered for controlling the four lighting functions and for connection to telephone/network and other electrical devices including nurse call systems.
- A patient-controlled pad is also available for nurse call and for simple control of the light functions.
- Available in silver.
- UL and CUL listed, and 10-year warranted.



A Division of Waldmann Lighting

Amadea Light



Amadea Control

	Purpose:	Lighting F	unctions:					
	Controlling the 4 light- ing functions.		\boxtimes	Pushbutton functions:				
	Connections to telephone and network.		Off All lamps are off.	on pad and control				
5 0	Connection of electrical devices.		Night Light (Push Once) Night light is on, all other lamps are off, 8 white LEDs illuminate on "Control."	Off Night light/Indirect ambient light				
	Integrated with nurse call system and			Reading light (green-backlit)				
	building wiring.			Purpose:				
1	Amadea Pad (Patient-operated unit).		Indirect Ambient Light (Push Twice) Indirect light is on, examination light and night light are off.	• Red-backlit pushbutton on Amadea Pad controls nurse call function.				
				 Simple control of the light functions. X Lighting systems off. 				
Pushb	utton functions:		Examination Light (Push Once) Indirect light, examination light and reading light are on, night light is off.	- Night light/Indirect ambient light.				
× c	Off			Reading light (pushbutton, green-backlit). For Control and Pad part numbers				
	light light/Indirect ambient light	0000	Indirect Ambient Light (Push Twice) Indirect light is on, examination light, reading	please call 800.634.0007				
E	xamination/Indirect ambient light		light and night light are off.					
R	Reading light (green-backlit)	0	Reading Light (Push Once) The reading light can be switched independently of the other lighting functions.					
חטטט	Part Number Body Color Ambient Lamp Ty	Light Light Li	ght Length Light Voltage Weight Opening (jockson) 1300	Derungs [®]				

	Part Number	Body Color Silver	Ambient Lamp Types		Reading Light	Night Light	Length	Light Opening	Voltage	Weight (lbs)
PRODUCT			2 x 54W T5HO	2x39W T5H0	1 x 24W T5H0		(inches)	(inches)	120V	(ius)
Amadea WLS	D13-929-000	Х	Х		Х	Х	48	46	Х	11
	D13-946-000	Х	Х			Х	48	46	Х	11
Amadea WSS	D13-945-000	Х		Х	Х	Х	36	34	Х	11
	D13-579-000-USA	Х		Х		Х	36	34	Х	11
Amadea WSS	D13-944-000	Х		Х			36	34	Х	11

For pricing, or additional ballast and technical information, please call 800.634.0007

www.waldmannlighting.com Phone 847.520.1060 • Fax 847.520.1730 Email: waldmann@waldmannlighting.com

UL)∪s

Medical Lighting

A Division of Waldmann Lighting 9 W. Century Drive, Wheeling, IL 60090 800.634.0007



Amadea Pad

